

HD110



> On/Off/Esc
HD110


> 가

> OK

가


> OK

가




- > Hold/min/max Hold 가
- > On/Off/Esc 가


- > Hol/min/max / , Hol/min/max
- > Hol/min/max / , Hol/min/max
- > Hol/min/max / , Hol/min/max
- > On/Off/Esc / ,




- > Select 가
- > UNIT 가
- > OK UNIT 가
- > Select 가 : °C or °F.
- > OK 가
- > UNIT 가
- > On/Off/Esc 가



- > AUTO OFF 가 Select
- > AUTO OFF OK
- > Select 가 : 15, 30, 45, 60, 75, 90, 105, 120, OFF
- > OK
- > AUTO OFF 가
- > On/Off/Esc



- > /
- > Select , BEEP 가
- > OK
- > OFF ON
- > Select , ON , OFF
- > OK
- > BEEP 가
- > On/Off/Esc



- > 가
- > 가
- > 가

- >
- > AAA LR03 1.5 V.
- > 가



Once returned to KIMO, required waste collection will be assured in the respect of the environment in accordance to 2002/96/CE guidelines relating to WEEE

www.kimo.fr

EXPORT DEPARTMENT
Boulevard de Beaubourg - Emerainville - BP 48
77312 MARNE LA VALLEE CEDEX 2
Tel : + 33.1.60.06.69.25 - Fax : + 33.1.60.06.69.29

